| Melitta® | Produ | ct Data Sheet | | |
|--|------------------------------|---------------------|----------------|--|
| COFFEE PREPARATION | | | EASY TOP TIMER | |
| Fechnical Data | | | | |
| Туре | 1010-15 | | 31 | |
| Power rating | 920 - 1080 | [W] | | |
| Voltage | 220 - 240 | [V] | | |
| Frequency | 50 / 60 | [Hz] | | |
| Weight | 1.45 | [kg] | | |
| Weight with packaging | 1.85 | [kg] | | |
| Height x Width x Depth | 302 x 167 x 247 | [mm x mm x mm] | | |
| Height x Width x Depth packaging | 316 x 287 x 190 | [mm x mm x mm] | | |
| Water tank volume | 1.375 | []] | | |
| Maximum amount of coffee | 10 / 1.25 | [cups]/[l] | | |
| Brewing time | 09:00 | [mm:ss] | | |
| Finish brew coffee | 81 | [°C] | | |
| Warmkeeping temperature (1h) | _ | [°C] | | |
| Automatic shut-off | 81 | | + | |
| Filter size | 20 / 40 / 60 | [min] | | |
| | 1x4 | | | |
| eature Details | | | | |
| Glass jug | | | | |
| - jug lid with one hand operation | | | | |
| - handle with finger protection a | and water volume in | dication (cup-wise) | | |
| - stainless steel band | | | | |
| - dishwasher safe | | | | |
| - stainless steel jug handle cov | ≏r | | | |
| Water tank | 01 | | | |
| - water level indication for 2 to 7 | 10 outpo / 2 to 15 outpo | 22 | | |
| | | μs | | |
| - double sided water level indic | ation | | | |
| - overflow hole | | | | |
| Filter | | | | |
| - swing filter with filter lock | | | | |
| - removable swing filter for easy | y cleaning | | | |
| - break-proof | | | | |
| - drip stop | | | | |
| - dishwasher safe | | | | |
| | - filter size 1x4 | | | |
| - swing filter with stainless stee | Loover | | | |
| | l cover | | | |
| Top cover | | | | |
| - hinged lid for water tank and f | ilter with double sid | ed handle | | |
| Housing | | | | |
| - high polished surfaces | | | | |
| Brewing system | | | | |
| - well-balanced brewing temper | rature for coffee ext | raction | | |
| Clock | | | | |
| - display of hours and minutes | | | | |
| - white background illumination | (possible to switch | -off) | | |
| Timer | (POSSIDIE TO SWITCH | 011/ | | |
| | | | | |
| - programmable start time | Lucha a sett | | | |
| - timer clock shown on display during setting | | | | |
| - white LED indication, when ac | tivated | | | |
| Automatic shut-off | | | | |
| - programmable warm keeping | time: 20, 40, or 60 | minutes | | |
| - factory setting 40 minutes | | | | |
| - warm keeping time shown on | display during settir | ng | | |
| - manual switch-off possible | | v | | |
| Power cord | | | | |
| - cord length 70 cm | | | | |
| | | | | |
| - storage under bottom cover | | | | |
| - power cord outlet on the bac | k | | | |
| | | | | |
| Approvals | | | | |
| Approvals - Safety approval (VDE-GS) - Food law approval | | | | |